WSF121.70G

Lavoce

12" GUITAR WOOFER

FERRITE MAGNET STEEL BASKET DRIVER



- 1.8 INCH COPPER VOICE COIL
- 99 dB/SPL SENSITIVITY
- 200 WATT PROGRAM POWER HANDLING
- SMOOTH AND SILKY TONE
- CONTROLLED LOW-END, FAT AND WARM MIDS, **DETAILED AND HARMONICALY RICH HIHGS**

GENERAL SPECIFICATIONS

Nominal diameter	mm (in.)	300 (12)	
Nominal impedance	Ω	8	
Minimum impedance	Ω	7,3	
Program power (1)	W	200	
AES Power rating (2)	W	100	
Sensitivity (3)	dB	99	
Frequency range	Hz	70 ÷ 5000	
Voice coil diameter	mm (in.)	45 (1.8)	
Chassis material	Steel		
Magnet material	Ferrite		
Magnet dimensions	mm	155 x 80 x 20	
OD x ID x h	(in.)	(6.14 x 3.15 x 0.79)	
Coil material	Copper		
Former material	Polyimide		
Cone material	Water Proof Treated Paper		
Surround material	Paper		
Xmax (4)	mm (in.)	2,3 (0.09)	
Xmech (5)	mm (in.)	6,3 (0.25)	
Gap height	mm (in.)	8 (0.31)	
Voice coil winding height	mm (in.)	8,6 (0.34)	
Driver displacement volume	I (ft³)	2,2 (0.08)	

SMALL SIGNAL PARAMETERS


DC resistance	Re	Ohm	6,6
Resonance frequency	Fs	Hz	75
Moving mass	Mms	g (oz)	33,2 (1.17)
Compliance	Cms	mm/N	0,13
Force factor	BxL	N/A	13,5
Mechanical Q-factor	Qms		11,0
Electrical Q-factor	Qes		0,56
Total Q-factor	Qts		0,54
Equivalent air volume	Vas	I (ft³)	48 (1.7)
Voice coil Inductance	Le	mH	0,57
Diaphragm area	Sd	cm² (in.²)	506 (78.43)
Reference efficiency	Eta 0	%	3,50

SHIPPING INFORMATION


WWW.LAVOCESPEAKERS.COM

Net weight	kg (lb.)	3,2 (7)
Multipack size (1)	mm	356 x 356 x 173
WxDxH	(in.)	(14 x 14 x 6.8)
Multipack weight	kg (lb.)	4,1 (9.1)

FREQUENCY RESPONSE



DIMENSIONS mm (in.)



(1) Program power is defined as 3 dB greater than AES Power. (2) Tested for two hours using a continuous, band-limited pink noise signal as per AES 2-1984 Rev. 2003. Loudspeaker tested in free air. (3) From T/S parameters, measured with Klippel DA LPM module. (4) The Xmax is calculated as: (Hvc - Hg)/2+ Hg/4. Hvc is the voice coil height and Hg the gap height. (5) The Xmach is calculated as: (Hvc - Hg)/2 + Hg-2). Hvc is the voice coil height and Hg the gap height. (6) Thiele-Small parameters are measured after preconditioning: a) at 20°C- 22°C, 50% humidity for 2 hours; b) by Klippel LSI measurement.

All specifications subject to change without notice_B.a



Lavoce Italiana